

GEL TAPE & GEL CHIP

Tape & Chip GEL. A Handy Performer.

α GEL

GELTEC

www.geltec.co.jp

GEL TAPE & GEL CHIP

■ Shock Absorption
■ Vibration Damping

【Features】

- ◆ Simply cut and attach where used. Adhesive agent used on one side.
- ◆ Selections (wide/thick) available for different use.
- ◆ Effective in narrow space where GEL insulators or bushes not usable.
- ◆ α GEL performs;
 - ① Usable from -40°C up to 100°C .
 - ② Low compression set. High weather and chemical resistance. Performance stays long.

【Specification】

◆ Gel Tape

Selection	L(mm)×W(mm)×T(mm)
GT-1	1,000×10×1
GT-2	1,000×20×1
GT-3	1,000×10×2
GT-4	1,000×20×2
GT-5	1,000×10×3
GT-6	1,000×20×3

*Feel free to contact GELTEC for custom size.

◆ Gel Chip

Selection	D(mm)×W(mm)×T(mm)
GC-1	10×10×3
GC-2	10×10×5
GC-3	15×15×3
GC-4	15×15×5
GC-5	15×15×10
GC-6	20×20×3
GC-7	20×20×5
GC-8	20×20×10

*Each selection is delivered in min. 25 pcs / lot.

【How to use】

- ◆ Remove dust from surface.
- ◆ Peel off first. Then be sure to attach and press evenly. Adhesive agent used.

【Applications : Shock Absorber】


- outdoor radio
- door hit
- packing



● outdoor radio



● durable α GEL packing



【Cautions】

- ◆ GEL surface is powdered to prevent stickiness.
- ◆ For ensuring application, customer's preliminary test suggested before use.
- ◆ GELTEC silicone products developed exclusively for general industrial use. NEVER apply for medical implant use.
- ◆ Data or values above are not guaranteed. Subject to change without prior notice.



http://www.geltec.co.jp
E-mail: tokyo@geltec.co.jp

Toyo-Suisan Bildg. 1F, 13-40, Konan 2-chome, Minato-ku, Tokyo, 108-0075 Japan.
TEL : +81-3-5461-4668 FAX : +81-3-5461-3208

ISO 9001 qualified (LRQA 961790)
ISO 14001 qualified (LRQA 772690)